

TA Indoor power wheelchair request for quote



0800 238 523
sales@mortonperry.co.nz

For comparison charts &
specifications visit:
mortonperry.co.nz

Client Name: _____ User weight: _____

Therapist: _____ Date: _____

Organisation: _____

☐ Enable ACC

☐ Enable MOH

☐ Accessable MOH

Standard Specifications* - No up-charge

- ☒ Power functions: tilt, elevate
- ☒ Manual back recline 50 degrees
- ☒ Turning radius 18"/45cm
- ☒ Base width 22"/56cm / chair length w/o footrest 27"/69cm
- ☒ 10" Front wheels
- ☒ Super low floor to seatpan 12"/38cm with power elevate
- ☒ RNET expandable electronics
- ☒ 2 Pole, 450w motors, Range max 22km
- ☒ The client can remain seated in the power wheelchair during vehicle transport. Safety crash tested design. ISO7179-19, NZ LVVTA 45-60 2.6.

TA Indoor



MOH
Enable
Category
C

Seat width & depth

Width

Junior

- | | | | |
|-------------------------------------|---------------------------------------|-------------------------------------|---------------------------------------|
| ☐ 10"/25.4cm | ☐ 18"/45.7cm | ☐ 10"/25.4cm | ☐ 18"/45.7cm |
| ☐ 12"/30.5cm | ☐ 20"/50.8cm | ☐ 12"/30.5cm | ☐ 20"/50.8cm |
| ☐ 14"/35.6cm | ☐ 21.5"/54.6cm | ☐ 14"/35.6cm | ☐ 21.5"/54.6cm |
| ☐ 16"/40.6cm | ☐ other _____ | ☐ 16"/40.6cm | ☐ other _____ |

Depth

TA Junior



MOH
Enable
Category
C

Power Functions - base

- At no charge: ☒ Tilt ☒ Elevate
- ☐ Back recline ☐ Power Centre

Floor to seat pan (F)

- | | |
|--|--------------------------------------|
| ☐ 15-16.75" *Standard | ☐ 19-19.75" |
| ☐ 17-17.75" | ☐ Other _____ |
| ☐ 18-18.75" | _____ |

*With TA power elevate functions

Maximum overall width

- ☐ 22"/56cm Standard

Lower leg support assembly

TA Indoor

- ☐ Manual - Centre
- ☐ Manual - 70° swing away - stepless L/H
- ☐ Manual - 70° swing away - stepless R/H

- ☐ Power Centre - standard (13"-18.5")
- ☐ Power Centre - short (10"-13.5")
- ☐ Power Centre - short (pivots under seat)
- ☐ Power Elevating - L/H
- ☐ Power Elevating - R/H

Junior

- ☐ Manual - Centre

Footplate

TA Indoor

- ☐ Manual centre - standard
- ☐ Manual centre - with pull up system
- ☐ Manual centre - wider with extended lip
- ☐ Divided left & right (pair)
- ☐ Electric flip-up
- ☐ Posterior foot support (heel loops)

Junior

- ☐ Manual centre - standard

Controller electronics

RNET Expandable is standard

- ☐ PG JSM LED w/o display (no lights) (standard on Indoor + Junior)
- ☐ PG JSM2 Large colour screen (can be used on chair fitted with LED lights)
- ☐ PG JSM2 Bluetooth Large colour screen
- ☐ PG JSM LED with lights (for chair fitted with LED lights)
- ☐ PG JSM Colour screen with lights (for chair fitted with LED lights)
- ☐ Attendant control dual - Standard
- ☐ Attendant control carer handle
- ☐ Head array

Back Configuration

- ☐ No upholstery
- ☐ Tall straight 1" - adjustable width (also for Junior)
- ☐ Contour design - adjustable width
- ☐ Contour design - adjustable width - Junior

Controller swing-away / dropdown

- ☐ Right hand side
- ☐ Left hand side
- ☐ Dropdown
- ☐ Swing-away

Stump support

- ☐ Left
- ☐ Right
- ☐ Both

Arm support

- ☐ Desk
- ☐ Flip-up
- ☐ Adult
- ☐ Full length
- ☐ Dual post flip-up
- ☐ Pediatric
- ☐ Standard leather
- ☐ Gel
- ☐ Gutter

Pelvic positioning belt


- ☐ Standard
- ☐ Small
- ☐ 2-point padded
- ☐ Medium
- ☐ 4-point padded
- ☐ Large

Tyres

- Drive tyres: ☐ Pneumatic (std) ☐ Solid

Leg Support

- ☐ Drop in seat guides
- ☐ Thigh guides - Med (10x13cm)
- ☐ Thigh guides - Lrg (13x15cm)



Min. seat to floor height = Lower leg length - cushion + clearance or Seat to floor

Seating - Cushion

☐ Not required	Size (width x height):	Covers:
☐ Vicair Active O2	6cm	_____
☐ Vicair Active O2	9cm	_____ Inco Comfair
☐ Vicair Adjuster O2	6cm	_____ ☐ ☐
☐ Vicair Adjuster O2	10cm	_____ ☐ ☐
☐ Vicair Adjuster O2	12cm	_____ ☐ ☐
☐ Vicair Vector O2	6cm	_____ ☐ ☐
☐ Vicair Vector O2	10cm	_____ ☐ ☐
☐ Nxt Biofit	10cm	_____ ☐ ☐
☐ Other (please specify)	_____	_____

VICAIR O2
ACTIVE 9



VICAIR O2
ADJUSTER 10



VICAIR O2
VECTOR 10



nxt
SEATING
Biofit



Seating - Back system

☐ Not required	Size (width x height):
☐ Nxt Xtend (AC)	_____
☐ Nxt Xtend Deep (PC)	_____
☐ Nxt Optima Carbon (AC)	_____
☐ Nxt Optima Carbon Deep (PC)	_____
☐ Other (please specify)	_____

nxt
SEATING
Xtend



nxt
SEATING
Optima Carbon



Headrest

☐ Not required	
☐ TA standard headrest (leather)	☐ TA Junior 5"
☐ Nxt Multifit - Contoured	☐ TA Junior 7"
☐ Nxt Multifit - Large	
☐ Nxt Multifit - Extra Large	
☐ Other (please specify) _____	

Includes headrest stem & brackets to attach to back system.



Nxt Large

Nxt Extra Large

Set-up Instructions

Accessories (view accessories catalogue on our website)